GETRIEBEBAU NORD Member of the NORD DRIVESYSTEMS Group



Technical Information / Datasheet

SK TIE4-M12-CAO

CANopen connection extension M12 BUS system connector

CANOPER

Part number: 275 274 501

Scope of delivery

1 x	M12 Plug connector	SK TIE4-M12-CAO
1 x	Cover cap	grey

As-delivered status with screwed-on connector cover



Field of use

The M12 Plug connector has open cable ends and wire end sleeves It is used to make a pluggable connection using normal commercial M12 round plug connectors. It connects the CANopen technology option with the incoming CANopen field bus cable at the input side.

Technical data

Version				
Temperature range	-30 +90 °C			
Contact insert Colour / Material	Grey / RAL 7042 Plastic			
Round plug connector Material	Metal, CuZn, nickel plated			
Connection / Type Round plug connector	M12x1, adjustable Plug connector with flexible strand M16x1.5, metric screw thread			
Contact insert Contacts / Coding	5 pin, A - coded			

Weight	23 g
Connector cover Colour / Material	Grey / RAL 7042 Plastic
Protection class (screwed)	IP67
Fastening	Hexagonal nut M16x1.5 *
Tightening torques * M12x1 Male socket connector M16x1.5 Screw thread	0.6 Nm 1.5 Nm

^{*} Suitable assembly spanner commercially available (see Installation)

Cable				
Number of conductors /	5 x 0.34 mm ²			
Cross section				
Wire strands / colours	UL / (wt, br, bl, bk, gr)			
Length of wire strands	250 mm			
Degree of fouling	3/2			

Mech. Service life	min. 100 plugging cycles
Operating voltage	max. 60 V
Current rating	4 A
Insulation resistance	≥ 10 ⁸ Ω


	Connection extension	SK TIE4-M12-CAO			
1.2	Extensive revision	2414	Bch	TI 275274501	EN
version	reason for change(s)	issue	name	document	speech



Circuit diagram









Installation / option locations

The M12 Receptacle connector are intended for direct installation in a free M16 hole / threaded opening of the device series (see below).

Device series	Recommended option location	Option locations		
SK 135E * SK 180E * SK 190E * Housing SK 1xxE xxx-xxx-x (-C))	4R / 4L (incoming) 5R / 5L (outgoing)			
SK 200E Frequency inverter connecting unit SK TI4-x-2xx-x (-C)	4R / 4L (incoming) 5R / 5L (outgoing) optional ** 6R / 6L, 7R / 7L, 8R / 8L	(4) (7) (3) (3) (4) (4) (4) (4) (4) (4) (4) (4) (4) (4		
BUS technology box BUS connection unit SK TI4-TU-BUS (-C)	1 / 2 / 3 / 4 optional *** 5R / 5L	(T) (2) (3) (4) (80)		

^{*} The configuration capability of the respective Receptacle connector depends on its functionality with regard to the device series, e.g. the SK TIE-M12-SH Socket connector cannot be installed with the SK 1xxE housing.

The installation position and mounting location (coding pin or coding groove on contact carrier) of the Socket connector is freely positionable and should be aligned (see installation step 6) such that angled M12 round connectors can also be connected in a way that avoids collisions.

The installation steps described in the following apply to the installation of the M12 Receptacle connectors in the housing and in the frequency inverter connecting unit or the BUS connecting unit of an external technology box.

Installation steps for installation of the M12 Receptacle connector

1		Remove M16 blind plug at the provided option location side (right / left) of the starter or frequency inverter housing or the connection unit.
		Remove M16 blind plug from the provided option location hole (bottom) of the BUS connection unit.
2	2.	Screw the middle hexagonal nut towards the front using a size 17 open-ended spanner.

2 / 5

^{**} Size 1 – 3 with optional SK TIE4-M12-M16 connection extension, size 4 direct installation

^{***} With optional SK TIE4-M20-M16 connection reduction



3.	EMC Twist associated wire pairs together (e. g. bus system, power supply, etc.).		3
4.	Screw M12 flanges component directly into the affected M12 threaded opening of the housing or connecting unit of the frequency inverter. Screw M12 Receptacle connector into the relevant M16 threaded opening of the BUS connecting unit.	33.000	
	Alternative option locations		
	Connection extension SK TIE4-M12-M16 The M12 Receptacle connector can alternatively be installed with an optional M12-M16 connection extension.	() ·	6
	First screw the M12 Receptacle connector directly into the connection extension and then fit into the M12 threaded opening in the connection unit. For more information see Optional accessories	000	/
	Connection reduction SK TIE4-M20-M16 The M12 Receptacle connector can alternatively be installed with an optional M20-M16 connection reduction. First screw the M12 Receptacle connector directly into the connection reduction and then fit into one of the side M12 threaded openings in the connection unit. For more information see Optional accessories		C
5.	Align coding pin / coding groove vertically to 12 o'clock by rotating the front hexagonal nut.	Socket connector Plug	connector
6.	Secure the front hexagonal nut with a 17 mm open-ended spanner. Screw the rear hexagonal nut to the connection unit or the starter or frequency inverter housing using a size 17 open-ended spanner or a special torque / installation wrench. Take the specified tightening torques into consideration, see technical data.		
7.	Ensure that the M12 round plug connector or the cover cap is properly screwed onto the M12 Receptacile connector and tightened.	Co G	

NOTICE Corrosion

Pay attention to leaktightness during the installation of all components (assembly, connection extension etc.). It must be ensured that all components are correctly seated and the tightening torques are adhered to when doing this.

In order to ensure that protection class **IP66** is complied with (concerns all devices with type key SK ...-C), another **pressure - leaktightness test** must be performed when the assembly work has been completed.

Failure to do this will allow moisture to penetrate the device, which will result in the risk of corrosion and short circuiting.

TI 275274501 - 2414 3 / 5



1 Information

Torque / assembly wrench



In order to provide a secure, sealed and vibration-proof connection, the M12 connection extensions, which are equipped with a hexagonal threaded ring (size 17), should be tightened with special torque / assembly wrenches. For professional installation NORD recommends the use of commercially available assembly tools (M12, size 17) with an adjustable, defined tightening torque (e.g. from Murrelektronik).

Connections

The open cable ends of the extension / M12 Plug connector are connected to the terminal strip of the BUS connection unit (technology box) or the BUS customer interface in the frequency inverter (see below).









BUS connection unit SK TI4-TU-BUS (-C) BUS technology box SK TU4-CAO (-M12) /(-C) BUS customer interface SK CU4-CAO

Electrical connections




Connection extension M12 Plug connector SK TIE4-M12-CAO BUS technology box SK TU4-CAO (-M12)/ (-C) BUS connection unit SK TI4-TU-BUS (-C)

BUS customer interface SK CU4-CAO

Contact assignments 5-pole Plug connector A-coded

Pin	Colour		Signal	Contact	Designation	Contact	Designation
1	white		Shield	9	SHLD	90	SHLD
2	Brown		+24 V	1	24V-B CAO	45	24V bus
3	Blue		GND	7	GND B CAO	46	GND Bus
4	Black		CAN_H	3	CAO+ OUT	75 (incoming)	CANopen+
5	grey		CAN_L	5	CAO- OUT	76 (incoming)	CANopen-







4/5 TI 275274501 - 2414



Optional accessories

1 Information

M12 / M20 screw openings





Conductive connection extensions made from brass SK TIE4-M12-M16 from M12 to M16 or connection reductions SK TIE4-M20-M16 from M20 to M16 are optionally available for installing the M12 connection extensions in an M12 or M20 screw opening. For more information, see further documentation.

Further documentation (<u>www.nord.com</u>)

Document	Designation
<u>BU 0180</u>	SK 180E, SK 190E frequency inverter manual
<u>BU 0200</u>	Frequency inverter manual SK 2xxE
BU 0260	CANopen for SK 200E manual
BU 0280	DEVICENET for SK 200E manual
TI 275280000	Bus connection unit SK TI4-TU-BUS
TI 275280500	Bus connection unit SK TI4-TU-BUS-C
TI 275274510	Connection extension SK TIE4-M12-M16
TI 275274511	Connection reduction SK TIE4-M20-M16
TI 275271001	CANopen bus interface SK CU4-CAO
TI 275281101	CANopen bus interface SK TU4-CAO

Document	Designation
TI 275281151	CANopen bus interface SK TU4-CAO-C
TI 275281201	CANopen bus interface SK TU4-CAO-M12
TI 275281251	CANopen bus interface SK TU4-CAO-M12-C
TI 275271002	DeviceNet bus interface SK CU4-DEV
TI 275281102	DeviceNet bus interface SK TU4-DEV
TI 275281152	DeviceNet bus interface SK TU4-DEV-C
TI 275281202	DeviceNet bus interface SK TU4-DEV-M12
TI 275281252	DeviceNet bus interface SK TU4-DEV-M12-C
TI 275274515	Connection extension SK TIE4-M12-CAO-OUT

TI 275274501 - 2414 5 / 5